


Bevel BuddyBox[®] H Series

*EXTREMELY EFFICIENT
RIGHT ANGLE SHAFT MOUNTED
REDUCERS AND GEARMOTORS.*



Features

- **Bevel Input + Helical Output = Extreme Efficiency**
Dependable hardened steel gearing
- **Lightweight, Compact Housing**
Easy installation with less load on the head shaft.
Aluminum construction provides high thermal capacity.
- **Maintenance Free and Lubed for Life**
Lowest total life cycle costs
- **Universal Mounting**
Install in any orientation without modification

Technical Specs

- High speed / low reduction ratio 5:1 ~ 20:1
- Motor capacity: 3 ~ 15 HP
- Max input: 3600 motor RPM (120 Hz)
- C-face Quill or Coupled and Integral motor models available. Available hollow shafts include Easy Grip bushings, keyed hollow bores or shrink discs

Industry



FACTORY AUTOMATION

HIGH SPEED UNIT HANDLING

Bevel BuddyBox[®] H Series

