

Drive Unit Nomenclature



Mounting for Upright	Shaft Arrangement	High Speed Shaft	Slow Speed Shaft	Option	Nominal Ratio																																				
(Blank)		M Right Angle Shaft Parallel Shaft	(Blank) Solid Shaft Hollow Shaft (Shrink Disk Type)	(Blank) Without Option	Right Angle Shaft																																				
					<table border="1"> <tr><td>6.3</td><td>56</td></tr> <tr><td>7.1</td><td>63</td></tr> <tr><td>8</td><td>71</td></tr> <tr><td>9</td><td>80</td></tr> <tr><td>10</td><td>90</td></tr> <tr><td>11.2</td><td>100</td></tr> <tr><td>12.5</td><td>112</td></tr> <tr><td>14</td><td>125</td></tr> <tr><td>16</td><td>140</td></tr> <tr><td>18</td><td>160</td></tr> <tr><td>20</td><td>180</td></tr> <tr><td>22.4</td><td>200</td></tr> <tr><td>25</td><td>224</td></tr> <tr><td>28</td><td>250</td></tr> <tr><td>31.5</td><td>280</td></tr> <tr><td>35.5</td><td>315</td></tr> <tr><td>40</td><td>355</td></tr> <tr><td>45</td><td>400</td></tr> <tr><td>50</td><td>450</td></tr> </table>	6.3	56	7.1	63	8	71	9	80	10	90	11.2	100	12.5	112	14	125	16	140	18	160	20	180	22.4	200	25	224	28	250	31.5	280	35.5	315	40	355	45	400
6.3	56																																								
7.1	63																																								
8	71																																								
9	80																																								
10	90																																								
11.2	100																																								
12.5	112																																								
14	125																																								
16	140																																								
18	160																																								
20	180																																								
22.4	200																																								
25	224																																								
28	250																																								
31.5	280																																								
35.5	315																																								
40	355																																								
45	400																																								
50	450																																								
W Wall Mount (Upright Mounting)		Y Flange for Motor (Right Angle Shaft)	 Hollow Shaft (Key Type)	B With Backstop	Parallel Shaft																																				
		J Motor Adapter (Parallel Shaft)			<table border="1"> <tr><td>6.3</td><td>56</td></tr> <tr><td>7.1</td><td>63</td></tr> <tr><td>8</td><td>71</td></tr> <tr><td>9</td><td>80</td></tr> <tr><td>10</td><td>90</td></tr> <tr><td>11.2</td><td>100</td></tr> <tr><td>12.5</td><td>112</td></tr> <tr><td>14</td><td>125</td></tr> <tr><td>16</td><td>140</td></tr> <tr><td>18</td><td>160</td></tr> <tr><td>20</td><td>180</td></tr> <tr><td>22.4</td><td>200</td></tr> <tr><td>25</td><td>224</td></tr> <tr><td>28</td><td>250</td></tr> <tr><td>31.5</td><td>280</td></tr> <tr><td>35.5</td><td>315</td></tr> <tr><td>40</td><td>355</td></tr> <tr><td>45</td><td>400</td></tr> <tr><td>50</td><td>450</td></tr> <tr><td></td><td>500</td></tr> </table>	6.3	56	7.1	63	8	71	9	80	10	90	11.2	100	12.5	112	14	125	16	140	18	160	20	180	22.4	200	25	224	28	250	31.5	280	35.5	315	40	355	45	400
6.3	56																																								
7.1	63																																								
8	71																																								
9	80																																								
10	90																																								
11.2	100																																								
12.5	112																																								
14	125																																								
16	140																																								
18	160																																								
20	180																																								
22.4	200																																								
25	224																																								
28	250																																								
31.5	280																																								
35.5	315																																								
40	355																																								
45	400																																								
50	450																																								
	500																																								

Drive Unit Selection

Drive Unit
 Selection Tables
 Dimension Tables

